

University of Wollongong

## Research Online

---

Faculty of Engineering and Information  
Sciences - Papers: Part A

Faculty of Engineering and Information  
Sciences

---

2017

### Optimisation of output factor measurements using the Magic Plate 512 silicon dosimeter array in small megavoltage photon fields

Kananan Utitsarn

*University of Wollongong*, ku566@uowmail.edu.au

Z A. Alrowaili

*University of Wollongong*, zaa931@uowmail.edu.au

Nauljun Stansook

*University of Wollongong*, ns938@uowmail.edu.au

Michael L. F Lerch

*University of Wollongong*, mlerch@uow.edu.au

Marco Petasecca

*University of Wollongong*, marcop@uow.edu.au

*See next page for additional authors*

Follow this and additional works at: <https://ro.uow.edu.au/eispapers>



Part of the [Engineering Commons](#), and the [Science and Technology Studies Commons](#)

---

#### Recommended Citation

Utitsarn, Kananan; Alrowaili, Z A.; Stansook, Nauljun; Lerch, Michael L. F; Petasecca, Marco; Carolan, Martin G.; and Rosenfeld, Anatoly B., "Optimisation of output factor measurements using the Magic Plate 512 silicon dosimeter array in small megavoltage photon fields" (2017). *Faculty of Engineering and Information Sciences - Papers: Part A*. 6568.

<https://ro.uow.edu.au/eispapers/6568>

Research Online is the open access institutional repository for the University of Wollongong. For further information contact the UOW Library: [research-pubs@uow.edu.au](mailto:research-pubs@uow.edu.au)

---

## Optimisation of output factor measurements using the Magic Plate 512 silicon dosimeter array in small megavoltage photon fields

### Abstract

We evaluate the impact of an air gap and optimization of this air gap for the MP512 silicon detector array when operated in dosimetry mode for small photon field measurements in solid water. We present output factor measurements for 6MV and 10 MV photon beams with the square field sizes ranging from 0.5 to 10 cm<sup>2</sup>. The size of the air gap above the MP512 detector was changed from 0.5, 1.0, 1.2, 2.0 and 2.6 mm. We compare the output factors measurements of the MP512 with EBT3 film and the MOSkin dosimeter. For the two photon energies investigated, we find that the output factor measured by the MP512 reduce with increasing air gap and reducing of field size. The reduction in output factor is most pronounced for the 0.5 and 1 cm<sup>2</sup> field sizes. The air gap of 0.5 mm and 1.2 mm showed good agreement with the EBT3 film and MOSkin output factor for 6 and 10 MV photon fields, respectively. The negligible effect on dosimetry for the field sizes larger than 4x4 cm<sup>2</sup> demonstrates that the electronic disequilibrium caused by small air gap only influences the dosimetry measurements for small fields. The study shows that the output factor reduction is enhanced by increasing of air gap and demonstrates that the optimal air gap for the MP512 at 6 and 10 MV photon fields is 0.5mm.

### Disciplines

Engineering | Science and Technology Studies

### Publication Details

Utitsarn, K., Alrowaili, Z., Stanook, N., Lerch, M., Petasecca, M., Carolan, M. & Rosenfeld, A. (2017). Optimisation of output factor measurements using the Magic Plate 512 silicon dosimeter array in small megavoltage photon fields. *Journal of Physics: Conference Series*, 777 (1), 012022-1-012022-5.

### Authors

Kananan Utitsarn, Z A. Alrowaili, Nauljun Stanook, Michael L. F Lerch, Marco Petasecca, Martin G. Carolan, and Anatoly B. Rosenfeld

## Optimisation of output factor measurements using the Magic Plate 512 silicon dosimeter array in small megavoltage photon fields

This content has been downloaded from IOPscience. Please scroll down to see the full text.

2017 J. Phys.: Conf. Ser. 777 012022

(<http://iopscience.iop.org/1742-6596/777/1/012022>)

View [the table of contents for this issue](#), or go to the [journal homepage](#) for more

Download details:

IP Address: 203.10.91.85

This content was downloaded on 14/03/2017 at 22:25

Please note that [terms and conditions apply](#).

You may also be interested in:

[Characterisation of a two-dimensional liquid-filled ion chamber detector array using flattened and unflattened beams for small fields, small MUs and high dose-rates](#)

Prabakar Sukumar, Candice McCallum, Alan R Hounsell et al.

[Validation of a prototype DiodeAir for small field dosimetry](#)

T S A Underwood, J Thompson, L Bird et al.

[Experimental determination of the lateral dose response functions of detectors to be applied in the measurement of narrow photon-beam dose profiles](#)

D Poppinga, J Meyners, B Delfs et al.

[The effect of very small air gaps on small field dosimetry](#)

P H Charles, S B Crowe, T Kairn et al.

[Linearization of EBT3 film dose response and virtual film dosimetry for SBRT quality assurance](#)

M Cai, B Archibald-Heeren, Y Wang et al.

[Solid-state detectors in megavoltage dosimetry](#)

Z Yin, R P Hugtenburg and A H Beddoe

[Pushing the boundaries of spatial resolution in dosimetry using polymer gels and radiochromic films](#)

G Heilemann, D Georg and A Berg

[The LA48 linear ion chamber array for IM beam characterization](#)

C Martens, C De Wagter and W De Neve

# Optimisation of output factor measurements using the Magic Plate 512 silicon dosimeter array in small megavoltage photon fields

K Utitsarn<sup>1</sup>, Z A Alrowaili<sup>1</sup>, N Stansook<sup>1</sup>, M Lerch<sup>1</sup>, M Petasecca<sup>1</sup>, M Carolan<sup>2</sup>, A Rosenfeld<sup>1</sup>

<sup>1</sup>Centre for Medical Radiation Physics, University of Wollongong, Australia

<sup>2</sup>Illawarra Cancer Care Centre, Wollongong hospital, Australia

E-mail: ku566@uowmail.edu.au

**Abstract.** We evaluate the impact of an air gap and optimization of this air gap for the MP512 silicon detector array when operated in dosimetry mode for small photon field measurements in solid water. We present output factor measurements for 6MV and 10 MV photon beams with the square field sizes ranging from 0.5 to 10 cm<sup>2</sup>. The size of the air gap above the MP512 detector was changed from 0.5, 1.0, 1.2, 2.0 and 2.6 mm. We compare the output factors measurements of the MP512 with EBT3 film and the *MOSkin* dosimeter. For the two photon energies investigated, we find that the output factor measured by the MP512 reduce with increasing air gap and reducing of field size. The reduction in output factor is most pronounced for the 0.5 and 1 cm<sup>2</sup> field sizes. The air gap of 0.5 mm and 1.2 mm showed good agreement with the EBT3 film and *MOSkin* output factor for 6 and 10 MV photon fields, respectively. The negligible effect on dosimetry for the field sizes larger than 4x4 cm<sup>2</sup> demonstrates that the electronic disequilibrium caused by small air gap only influences the dosimetry measurements for small fields. The study shows that the output factor reduction is enhanced by increasing of air gap and demonstrates that the optimal air gap for the MP512 at 6 and 10 MV photon fields is 0.5mm.

## 1. Introduction

Modern radiation treatment techniques such as Stereotactic Radiosurgery (SRS) and Stereotactic Body Radiation Therapy (SBRT) are increasingly being used in cancer treatment. Large doses per fraction of SRS/SBRT are delivered in small photon radiation fields leading to steep dose gradients, Quality assurance (QA) is needed to ensure that the delivered dose matches the plan dose distribution [1]. Current commercial dosimetric QA tools for SRS/SBRT include ionization chambers, used for point dose measurements, as well as two-dimensional diode arrays and pixelated ionization chamber arrays. One limitation of the ionization chamber is that the dosimetry in small field can be perturbed by the chamber volume averaging effect [2]. Film has good spatial resolution but their processing is time consuming. ArcCHECK (Sun Nuclear, Melbourne, FL) contain an array of 1386 diodes distributed in a cylindrical acrylic phantom. To perform the patient QA, the treatment plan needs to be transferred to the QA system. The Delta4 (ScandiDos, Uppsala, Sweden), which consist of 1069 silicon diodes in a crossed array inside a cylindrical polymethylmethacrylate (PMMA) phantom, requires the recalculation of the dose on a CT scan phantom for the verification procedure. The operation system of both ArcCHECK and Delta4 is performed on the treatment couch [3] and is not designed to operate in transmission mode. In small irradiation field dose delivery via SRS and SBRT, the QA procedure needs



to have a detector with high spatial resolution. The Magic Plate 512 (MP512) a two dimensional monolithic silicon detectors array has a spatial resolution of 2 mm (pitch of array elements), which is suitable for such small field dosimetry. The patient treatment verification can be performed without the need to transfer the treatment plan to the detector and real time dose measurement can be made [4]. The purpose of this study is to examine the effect a small air gap immediately above surface of the MP512 has on the measured output factors for 6 and 10 MV photon fields as part of QA in SBRT and SRS.

## 2. Methodology


MP512 is a silicon monolithic detector manufactured on a p-type substrate. The MP512 array consists of 512 pixels with size  $0.5 \times 0.5 \text{ mm}^2$  and pitch 2 mm with an overall dimension of  $52 \times 52 \text{ mm}^2$ . The MP512 monolithic detector is wire bonded on a printed circuit board 0.5 mm thick and covered by a thin layer of resin to protect the bonding wires as well as the silicon detector surface from moisture [4]. The output factor measured with MP512 is compared with similar measurement using EBT3 films as well as *MOSkin* dosimeters. The MP512 was placed on a solid water phantom at the depth of 10 cm with 10 cm additional back scatter material and was aligned at the centre of the beam. The measurements were carried out with size of the air gap above the detector set at 0.5, 1.0, 1.2, 2.0 and 2.6 mm. The field size was varied from  $0.5 \times 0.5 \text{ cm}^2$  to  $10 \times 10 \text{ cm}^2$  while SSD was 90 cm. The measurements were performed on a Varian 21XI linear accelerator with 6 MV and 10 MV photon beams and dose rate 600 MU/min. In each case 100 MU was delivered with open field.

## 3. Results


Figure 1 shows the output factor for 6 MV measured by MP512 at 10 cm depth in a PMMA phantom for different air gaps above detector. Also shown air data from equivalent measurements performed using EBT3 film and *MOSkin*, with no air gap above them however. All measurements are normalized to the response in a  $10 \times 10 \text{ cm}^2$  field size. For small field sizes ( $0.5$  and  $1 \text{ cm}^2$ ) at 6 MV, the MP512 measured output factor reduces with increasing air gap above the detector. This reduction is significant when the air gap increases beyond 2mm. For larger field sizes ( $\geq 2 \times 2 \text{ cm}^2$ ) at 6 MV, we observe a small but increasing effect on the measured output factor with increasing air gap. The optimum MP512 air gap is 0.5 mm as it shows good agreement with the EBT3 film and *MOSkin* output factor. Figure 2 shows the output factor for 10 MV photons measured by MP512 with different air gaps above detector compared to the EBT3 film and *MOSkin* (with no air gap), normalised to the MP512 response at  $10 \times 10 \text{ cm}^2$  field size. For all field sizes at 10 MV, the MP512 measured output factor reduces with increasing air gap above the detector. The output factor measured by MP512 with air gap size of 1.2 mm seems to match best to the output factors measured with the EBT3 and *MOSkin*.

## 4. Conclusion

The output factors measured by the 2D detector array MP512 with different air gaps immediately above the detector placed at a depth of 10 cm in solid water phantom have been measured in both 6 and 10 MV photon fields. The properties of the array confirmed suitability for use as a phantom dosimeter for QA in SRS and SBRT. The output factor measured by MP512 with an air gap of 0.5 mm and 1.2 mm matches to within 2% that measured by GAF<sup>TM</sup> film and *MOSkin*<sup>TM</sup> for field sizes down to  $0.5 \times 0.5 \text{ cm}^2$ , for 6 and 10 MV, photon field respectively.



**Figure 1.** Field size response of MP512, EBT3 film and MOSkin for 6 MV photon beam normalized to the response at 10 x 10 cm<sup>2</sup> field size at depth 10cm in a PMMA phantom for different airgaps. (a) 0.5 mm, (b) 1.0 mm, (c) 1.2 mm, (d) 2.0 mm and (e) 2.6 mm



**Figure 2.** Field size of MP512, EBT3 film and MOSkin for 10 MV photon beam normalized to the response at 10 x 10 cm<sup>2</sup> field size at 10 cm depth in PMMA phantom. (a) 0.5 mm, (b) 1.0 mm, (c) 1.2 mm, (d) 2.0 mm and (e) 2.6 mm

## 5. Reference

- [1] Martin A and Gaya A 2010 *Clin. Oncol.* **22** 157-72
- [2] Low D A *et al* 2003 *Med. Phys.* **30** 1706-11
- [3] Li G *et al* 2013 *J. Appl. Clin. Med. Phys.* **14** 13-24
- [4] Aldosari A H *et al* 2014 *Med. Phys.* **41** 091707